



Main

Range of product	Harmony iPC
Product or component type	Profibus DP communication module
Accessory / separate part category	Connection accessory

Complementary

Accessory / separate part destination	Harmony iPC
Integrated connection type	Mini PCIe full-size with 1 SUB-D 9, transmission rate: 9.6...12 Mbit/s2 m cable
Input current	650 mA at 3.3 V DC
Range compatibility	Harmony iPC
Width	76 mm
Height	81 mm
Depth	36 mm

Environment

Ambient air temperature for operation	-20...60 °C
Ambient air temperature for storage	-40...85 °C
Relative humidity	5...95 % non-condensing

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	5.500 cm
Package 1 Width	13.900 cm
Package 1 Length	16.100 cm
Package 1 Weight	107.000 g
Unit Type of Package 2	S04
Number of Units in Package 2	4
Package 2 Height	30.000 cm
Package 2 Width	40.000 cm
Package 2 Length	60.000 cm
Package 2 Weight	432.000 g

Offer Sustainability

EU RoHS Directive	Not applicable, out of EU RoHS legal scope
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.