



Main

Range of product	Harmony iPC
Product or component type	Serial line interface
Accessory / separate part category	Connection accessory

Complementary

Accessory / separate part destination	Harmony iPC
Integrated connection type	Mini PCIe full-size with 2 female SUB-D 9 RS232, transmission rate: 50 bit/s...230.4 kbit/s2 m cable
Input current	400 mA at 3.3 V DC
Range compatibility	Harmony iPC
Width	76 mm
Height	81 mm
Depth	38.2 mm


Environment

Ambient air temperature for operation	-20...60 °C
Ambient air temperature for storage	-40...85 °C
Relative humidity	5...95 % non-condensing

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	5.4 cm
Package 1 Width	13.8 cm
Package 1 Length	16 cm
Package 1 Weight	40 g
Unit Type of Package 2	S01
Number of Units in Package 2	4
Package 2 Height	15 cm
Package 2 Width	15 cm
Package 2 Length	40 cm
Package 2 Weight	395 g
Unit Type of Package 3	S02
Number of Units in Package 3	4
Package 3 Height	15 cm
Package 3 Width	30 cm
Package 3 Length	40 cm
Package 3 Weight	512 g

Offer Sustainability

EU RoHS Directive	Not applicable, out of EU RoHS legal scope
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins