



Main

Range of product	ConneXium
Product or component type	Ethernet TCP/IP unmanaged switch
Concept	Transparent Ready
Communication port protocol	Ethernet TCP/IP
Port Ethernet	10/100BASE-TX - 4 port(s) copper cable 100BASE-FX - 1 port(s) fiber optic
Maximum number of switches in cascade	Unlimited

Complementary

Integrated connection type	Shielded RJ45 copper cable Duplex SC fiber optic
Transmission support medium	Twisted shielded pairs cable CAT 5E for copper cable Multimode optical fiber for fiber optic
Maximum cable distance between devices	100 m copper cable
Optic fiber length	4 Km 62.5/125 µm 5 km 50/125 µm
Attenuation	0...11 DB (62.2/125 µm) 0...8 dB (50/125 µm)
[Us] rated supply voltage	12...24 V
Supply voltage limits	9.6...32 V DC SELV
Power consumption in W	3.9 W
Electrical connection	Removable connector 3 ways power supply
Mounting support	35 mm symmetrical DIN rail
Marking	CE UL RCM
Local signalling	1 LED (green) for power supply 1 LED per channel (yellow) for data rate (ETH LINK) 1 LED per channel (green) for link status 1 LED per channel (green) for fiber port state
Ethernet cabling system	TF switches
Width	25 mm
Height	114 mm
Depth	79 mm
Net weight	0.12 kg

Environment

Ambient air temperature for operation	0...60 °C
Relative humidity	0...95 % non-condensing
IP degree of protection	IP30
Directives	2014/35/EU - low voltage directive 2014/30/EU - electromagnetic compatibility
Standards	UL 61010 EN/IEC 61131
Product certifications	CE[RETURN]UL[RETURN]RCM

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	 End Of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	18 months
----------	-----------

Power Wiring

