

Product data sheet

Characteristics

DE1KS217A04

TeSys LG - enclosure for DOL starter - without pushbuttons



Main

Range of product	TeSys
Range	TeSys
Device short name	DE1K
Product or component type	Enclosure
Device application	Motor
Material	Polycarbonate
Device composition	Contacteur ordered separately Circuit-breaker ordered separately
Product compatibility	LG7
Control type	Without

Complementary

Device mounting	Surface
Cable entry number	4 2 Pg 13 + 2 Pg 16 top 4 2 Pg 13 + 2 Pg 16 bottom
Height	165 mm
Width	175 mm
Depth	127 mm
Net weight	0.5 kg







Environment

IP degree of protection	IP55 conforming to IEC 60529
IK degree of protection	IK07 conforming to IEC 60529
Environmental characteristic	Standard environment
Product certifications	UKCA

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	20.500 cm
Package 1 Width	25.500 cm
Package 1 Length	28.500 cm
Package 1 Weight	982.000 g
Unit Type of Package 2	P06
Number of Units in Package 2	12
Package 2 Height	75.000 cm
Package 2 Width	60.000 cm
Package 2 Length	80.000 cm
Package 2 Weight	24.952 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant  EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	 End Of Life Information

Contractual warranty

Warranty	18 months
----------	-----------