

Product data sheet

Characteristics

DE1KS217A06A37

TeSys LG - enclosure for DOL starter - with 2 pushbuttons - emergency stop



Main

Range of product	TeSys
Range	TeSys
Device short name	DE1K
Product or component type	Enclosure
Device application	Motor
Material	Polycarbonate
Device composition	Contacteur ordered separately Circuit-breaker ordered separately Padlocking device
Product compatibility	LG7
Control type	Push-button start white I Push-button stop black O Mushroom head push-button emergency stop red

Complementary

Device mounting	Surface
Cable entry number	4 2 Pg 13 + 2 Pg 16 top 4 2 Pg 13 + 2 Pg 16 bottom
Height	165 mm
Width	175 mm
Depth	157 mm
Net weight	0.5 kg







Environment

IP degree of protection	IP55 conforming to IEC 60529
IK degree of protection	IK07 conforming to IEC 60529
Environmental characteristic	Standard environment
Product certifications	UKCA

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	21.4 cm
Package 1 Width	23 cm
Package 1 Length	26 cm
Package 1 Weight	1.155 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant  EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	 End Of Life Information

Contractual warranty

Warranty	18 months
----------	-----------