

Product data sheet

Characteristics

CSU76012004

Stago - KB184 tray perforated 60x200mm
L=3m 1mm pre-galvanized



Main

Range of product	Stago
Product or component type	Cable tray
Cable support type	Perforated
Mounting location	Partly outdoor environment with low exposure to corrosion ware-houses and parking garages

Complementary



Product destination	KB184 cable tray
Fixing mode	Screwless
Material with surface treatment	Steel pre-galvanized
Corrosion class	C2
Thickness	1 mm
Perforation location	Side perforation
Nominal cross section	12000 mm ²
Height	60 mm
Width	200 mm
Length	3 m
Net weight	2.299 kg / 100 m

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	6 cm
Package 1 Width	20 cm
Package 1 Length	300 cm
Package 1 Weight	2.299 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration

RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	No need of specific recycling operations