



Main

Range	Mureva
Product name	Mureva Enclosure
Product or component type	Weatherproof enclosure
Enclosure type	Enclosure for power outlet
Mounting plate description	Without mounting plate

Complementary

Enclosure mounting	Surface
9 mm pitches	8
Number of 18 mm modules per row	4
Total number of 18 mm modules	4
Number of horizontal rows	1
Electrical insulation class	Double insulation Class II
Number of openings of interface	1
Type of front cover	Transparent
Power dissipation in W	10 W
[In] rated current	63 A
Type of rail	DIN
Number of pre-cutouts PG ISO	1
Locking options description	Optional keylock
Enclosure material	Housing: self-extinguishing polymer
Net weight	0.425 kg
Base dimension	65 x 85 mm
Width	98 mm
Height	248 mm
Depth	98 mm
Internal depth	61 mm
Colour	Door: transparent green Enclosure: light grey (RAL 7035)



Environment

Standards	EN 62262 IEC 60695-2-1 IEC 61439-3 EN 50262 IEC 60670
Fire resistance	650 °C conforming to IEC 60695-2-1
IP degree of protection	IP65 conforming to IEC 60529
IK degree of protection	IK09 conforming to EN 50102
Environmental characteristics (UV)	UV resistant: class 3 conforming to ISO 4582:2010 Ultraviolet degradation test conforming to ISO 4892-2:2013
Overvoltage category	II
Ambient air temperature for operation	-25...40 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	9.700 cm
Package 1 Width	9.800 cm
Package 1 Length	24.500 cm
Package 1 Weight	395.000 g
Unit Type of Package 2	BB1
Number of Units in Package 2	8
Package 2 Height	21.800 cm
Package 2 Width	34.300 cm
Package 2 Length	40.000 cm
Package 2 Weight	3.400 kg
Unit Type of Package 3	P12
Number of Units in Package 3	192
Package 3 Height	100.000 cm
Package 3 Width	80.000 cm
Package 3 Length	120.000 cm
Package 3 Weight	94.392 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	No need of specific recycling operations
Halogen content performance	Halogen free product
Minimum percentage of recycled plastic content	26

Contractual warranty

Warranty	18 months
----------	-----------