



Main

Range	Wibe
Product name	Wibe Cable Ladders
Product or component type	Reinforced cable ladder
Device short name	KHZPV
Device application	Industrial application

Complementary

Type of side profile	Closed profile
Type of rung	Perforated profile
Mounting location	Indoor Outdoor
Rung spacing	250 mm
Material with surface treatment	Steel, Zinkpox coated white
Corrosion class	C5-I
Height	150 mm
Width	300 mm
Length	6 m
Net weight	448 kg / 100 m

Environment

Mounting location	Area with almost permanent high levels of humidity and airborne pollution tunnels and dockyards
Standards	IEC 61537

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	5.5 cm
Package 1 Width	29.7 cm
Package 1 Length	600 cm
Package 1 Weight	26.9 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes

RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
