



Main

| | |
|---------------------------------|-------------------------|
| Range of product | Harmony 9001K |
| Product or component type | Illuminated push-button |
| Device short name | K |
| Type of operator | Spring return |
| Operator profile | Clear projecting |
| Operator additional information | Without guard |

Complementary

| | |
|--------------------------------|----------------------------|
| Bezel material | Chromium plated metal |
| Mounting diameter | 30 mm |
| Light source | incandescent |
| Bulb base | BA 9s |
| Light block supply | Via integral transformer |
| [Us] rated supply voltage | 220...240 V AC |
| Contacts type and composition | 1 C/O |
| Connections - terminals | Screw clamp terminals |
| Operating position | Any position |
| [Ie] rated operational current | 10 A, AC-15 10 A, DC-13 |
| Contact operation | Standard |
| Device presentation | Complete product |

Environment

| | |
|---------------------------|---|
| Product certifications | CSA LR 25490 class 3211 03[RETURN]UL listed file E42259 CCN NKC[R][RETURN]CE[RETURN]NEMA |
| NEMA degree of protection | NEMA 1/2/3/3R/4/6/12/13 |

Packing Units

| | |
|------------------------------|-----------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Height | 4.826 cm |
| Package 1 Width | 5.842 cm |
| Package 1 Length | 11.43 cm |
| Package 1 Weight | 226.796 g |