

9001SK46J35LGFG

Illuminated selector switch head, Harmony
9001SK, plastic, long handle, green, 30mm, 3
positions, stay put, LED green, 24-28V



Main

Range of product	Harmony 9001SK
Product or component type	Head for illuminated selector switch
Device short name	9001SK
Type of operator	Stay put
Operator profile	Green long handle

Complementary

Bezel material	Plastic
Mounting diameter	30 mm
Net weight	0.19 kg
Shape of signaling unit head	Octagonal
Operator position information	3 positions
Contacts type and composition	Without contact block
Mechanical durability	500000 cycles
Light block supply	Direct
Light source	LED
Bulb base	BA 9s
Light block colour	Green
Product compatibility	9001KA1, mounted side 2
[Us] rated supply voltage	24...28 V AC/DC
Mounting location	Side 2
Device presentation	Basic element
Compatibility code	9001SK
Cap/operator or lens colour	Green
[Us] rated supply voltage	24...28 V
Light source colour	Green
Operator profile	Long handle
Type of operator	Stay put
Size	30 mm
Light source	LED
Cam profile	6

Environment

Protective treatment	TC
Ambient air temperature for storage	-40...70 °C
Ambient air temperature for operation	-25...70 °C
Electrical shock protection class	Class II conforming to IEC 61140
IP degree of protection	IP66 conforming to IEC 60529

NEMA degree of protection	NEMA 1 NEMA 12 NEMA 13 NEMA 2 NEMA 3 NEMA 3R NEMA 4 NEMA 4X
Standards	EN/IEC 60947-5-4 EN/IEC 60947-1 UL 508 JIS C 4520 CSA C22.2 No 14 JIS C 852 EN/IEC 60947-5-1
Product certifications	NEMA[RETURN]UL 508
Vibration resistance	7 gn (f= 2...500 Hz) conforming to IEC 60068-2-6
Shock resistance	50 gn conforming to IEC 60068-2-27

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.572 cm
Package 1 Width	5.334 cm
Package 1 Length	9.144 cm
Package 1 Weight	226.796 g

Contractual warranty

Warranty	18 months
----------	-----------