



Main

Range	Altira
Range of product	Altira
Product or component type	Switch
Device presentation	Mechanism
Cover plate colour tint	White (RAL 9010)

Complementary

Wiring device mounting	Surface Flush
Device mounting	Flush Surface
Product destination	Fixing frame OptiLine 45 installation system
Switch function	2-pole switch
Rated current	16 A at 250 V AC
Actuator	Rocker
Number of modules	2 modules
Fixing mode	Clip-in
Connections - terminals	4 screwless terminals
Clamping connection capacity	2 x 1.5...2 x 2.5 mm ² for rigid cable(s) 2 x 1.5...2 x 2.5 mm ² for solid stranded cable(s)
Material	PC: mechanism cover
Surface treatment	Untreated
Surface finish	Satin
Embedding depth	21 mm
Height	45 mm
Width	45 mm
Depth	28 mm
Net weight	0.033 kg
Market segment	Residential Small commercial

Environment

Standards	IEC EN 60669-1
Ambient air temperature for operation	-5...50 °C
Ambient air temperature for storage	-15...60 °C
IK degree of protection	IK04
IP degree of protection	IP21D
Environmental characteristic	Acetone Window-cleaning fluid Hydrogen peroxide (H2O2) Alcohol Liquid soap Bleach Petrol Oil UV resistant

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.5 cm
Package 1 Width	4.8 cm
Package 1 Length	4.5 cm
Package 1 Weight	32 g

Contractual warranty

Warranty	18 months
----------	-----------