



Main

Range	Altira
Product or component type	Socket-outlet
Range compatibility	OptiLine 45 fixing frame OptiLine 70 with Altira adaptor fixing frame
Device presentation	Mechanism
Number of power socket outlets	1 x 2P + E, German
Outlet standard description	Side earth
Socket additional information	Shuttered
Colour tint	Cover plate: white (RAL 9010)

Complementary

Product destination	Fixing frames
Range compatibility	OptiLine 45 OptiLine 70 with Altira adaptor
Ground lug position	Slanted 45° position
Rated current	16 A at 250 V AC 50/60 Hz
Number of modules	2 modules
Fixing mode	Clip-in
Connections - terminals	Screwless terminals
Clamping connection capacity	4 x 1.5...4 x 2.5 mm ² for rigid cable(s) 4 x 1.5...4 x 2.5 mm ² for solid stranded cable(s)
Material	PC: mechanism cover
Surface treatment	Untreated
Surface finish	Satin
Standards	IEC 60884-1 EN 60529 EN 62262 NF C 61-314
Height	45 mm
Width	45 mm
Depth	39 mm
Net weight	0.032 kg

Environment

Ambient air temperature for operation	5...50 °C
Ambient air temperature for storage	-15...60 °C
IK degree of protection	IK02
IP degree of protection	IP20
Environmental characteristic	Petrol Alcohol Bleach Window-cleaning fluid Acetone Liquid soap Hydrogen peroxide (H2O2) Oil UV resistant

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.2 cm
Package 1 Width	4.5 cm
Package 1 Length	4.5 cm
Package 1 Weight	32 g

Offer Sustainability

Sustainable offer status	Green Premium product
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------