



Main

Range	Altira
Product or component type	R-TV/SAT socket
Device presentation	Mechanism
Cover plate colour tint	White (RAL 9010)
Wiring device additional information	Return channel available at FM end Recommended for network cables For all types of TV/FM installation
Market segment	Residential Small commercial

Complementary

TV connector	Male IEC 9.52 mm
Radio connector	Female IEC 9.52 mm
SAT connector	Female F type
Number of modules	2 modules
Number of outputs	3
Product destination	OptiLine 45 installation system
Connections - terminals	1 screw terminals
Material	ABS + PC
Surface finish	Satin
Device mounting	Surface Flush
Fixing mode	Clip-in
Height	45 mm
Width	45 mm
Depth	29 mm
Embedding depth	17.9 mm
Net weight	0.059 kg

Environment

IP degree of protection	IP20
IK degree of protection	IK02
Ambient air temperature for operation	5...50 °C
Ambient air temperature for storage	-15...60 °C
Environmental characteristic	Hydrogen peroxide (H2O2) Bleach Acetone Petrol Oil UV resistant Liquid soap Window-cleaning fluid Alcohol
Standards	EN 62262 EN 60529

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.5 cm
Package 1 Width	7 cm
Package 1 Length	7 cm
Package 1 Weight	90 g

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	No need of specific recycling operations
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	18 months
----------	-----------