



Main

| | |
|---------------------------|-------------------|
| Range name | Anya |
| Product or component type | Switch |
| Function | Intermediate |
| Delivery form | Complete product |
| Rated current | 10 AX at 250 V AC |
| Cover plate color | White |
| Cover frame color | White |
| Kind of terminals | Lift terminals |

Complementary

| | |
|---------------------------|---------------------------------------|
| Installation | Flush |
| Power range | 2300 W |
| Terminal capacity | 2 cable(s) 2.5 mm ² |
| Wire structure | Flexible Rigid |
| Material of visible parts | ABS (acrylonitrile butadiene-styrene) |
| Surface finish | Gloss |
| Height | 81.5 mm |
| Width | 81.5 mm |
| Depth | 42 mm |
| Depth of visual part | 14 mm |
| Net weight | 0.088 kg |

Environment

| | |
|-------------------------|---------------|
| Standards | IEC 60669-1 |
| Product certifications | UKR[RETURN]CE |
| IP degree of protection | IP20 |

Packing Units

| | |
|------------------------------|---------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Height | 8.15 cm |
| Package 1 Width | 8.15 cm |
| Package 1 Length | 4.2 cm |
| Package 1 Weight | 86.23 g |