



Main

Range name	Anya
Function	Rotary dimmer
Delivery form	Complete product
Cover plate color	White
Cover frame color	White
Kind of terminals	Pillar terminals

Complementary

Installation	Flush
Dimmer application	Resistive load Inductive load
Load type	12 V AC halogen lamp with standard transformer: 60...500 W 230 V AC halogen lamp: 60...500 W 230 V AC incandescent lamp: 60...500 W
Rated voltage	230 V AC 50 Hz
Terminal capacity	1 cable(s) 2.5 mm ²
Wire structure	Rigid Flexible
Wire stripping length	7 mm
Material of visible parts	ABS (acrylonitrile butadiene-styrene): central plate ABS (acrylonitrile butadiene-styrene): cover frame ABS (acrylonitrile butadiene-styrene): knob
Surface finish	Gloss
Height	81.5 mm
Width	81.5 mm
Depth	50 mm
Depth of visual part	19 mm
Net weight	0.117 kg

Environment

Product certifications	CE[RETURN]UKR
IP degree of protection	IP20

Offer Sustainability

Sustainable offer status	Green Premium product
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.