



Main

Range name	Anya
Product or component type	Socket-outlet
Outlet standard description	Side earth
Socket number	1
Outlet poles configuration	2P + E
Delivery form	Complete product
Rated current	16 A at 250 V AC
Cover plate color	White
Cover frame color	White
Kind of terminals	Lift terminals

Complementary

Installation	Flush
Power range	3680 W
Terminal capacity	2 cable(s) 2.5 mm ²
Wire structure	Rigid Flexible
Wire stripping length	12 mm
Material of visible parts	ABS (acrylonitrile butadiene-styrene): cover frame ABS + PC: central plate
Surface finish	Gloss
Height	81.5 mm
Width	81.5 mm
Depth	34 mm
Depth of visual part	11 mm
Net weight	0.096 kg

Environment

Standards	IEC 60884-1
Product certifications	UKR
IP degree of protection	IP20

Packing Units

Package 1 Weight	87.500 g
Package 1 Height	81.500 mm
Package 1 Width	81.500 mm
Package 1 Length	34.000 mm

Contractual warranty

Warranty	18 months
----------	-----------