

## Product data sheet

### Characteristics

## DF2FGA100

DIN cartridge fuses, TeSys GS, blade size DIN NH00, fuse type aM, 690VAC, 100A, without striker, set of 3 parts



### Main

Range of product	DF
Product or component type	Fuses
Device short name	blade fuse
[Ue] rated operational voltage	690 V AC
Fuse size	NH00
Fuse type	DIN

### Complementary

[In] rated current	100 A
Fuse curve	AM
Quantity per set	Set of 3
Net weight	0.16 kg

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
PVC free	Yes
California proposition 65	WARNING: Cancer and Reproductive Harm - <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>

### Contractual warranty

Warranty	18 months
----------	-----------