

# GS1AH02

Direct rotary handle, TeSys GS, black handle, right side mounting, 2 positions I-O, for GS 100 to 400A IEC



## Main

|                           |                                                                                                                                            |
|---------------------------|--------------------------------------------------------------------------------------------------------------------------------------------|
| Range of product          | TeSys                                                                                                                                      |
| Range                     | TeSys                                                                                                                                      |
| Device short name         | GS1AH                                                                                                                                      |
| Product or component type | Rotary handle                                                                                                                              |
| Range compatibility       | TeSys TeSys GS GS1 J<br>TeSys TeSys GS GS1 K<br>TeSys TeSys GS GS1 L<br>TeSys TeSys GS GS1 N<br>TeSys TeSys GS GS1P<br>TeSys TeSys GS GS1Q |
| Type of operating handle  | Direct right side                                                                                                                          |
| Handle colour             | Black                                                                                                                                      |

## Complementary

|                          |                                                    |
|--------------------------|----------------------------------------------------|
| Handle positions         | O-I                                                |
| Rotary handle padlocking | With                                               |
| Switch rated current     | 100 A<br>125 A<br>160 A<br>250 A<br>315 A<br>400 A |
| Standards                | IEC                                                |
| Net weight               | 0.1 kg                                             |

## Packing Units

|                              |           |
|------------------------------|-----------|
| Unit Type of Package 1       | PCE       |
| Number of Units in Package 1 | 1         |
| Package 1 Height             | 8.000 cm  |
| Package 1 Width              | 3.000 cm  |
| Package 1 Length             | 17.000 cm |
| Package 1 Weight             | 85.900 g  |
| Unit Type of Package 2       | S02       |
| Number of Units in Package 2 | 20        |
| Package 2 Height             | 15.000 cm |
| Package 2 Width              | 30.000 cm |
| Package 2 Length             | 40.000 cm |
| Package 2 Weight             | 2.066 kg  |

## Offer Sustainability

|                          |                                |
|--------------------------|--------------------------------|
| Sustainable offer status | Green Premium product          |
| REACH Regulation         | REACH Declaration              |
| REACH free of SVHC       | Yes                            |
| EU RoHS Directive        | Compliant  EU RoHS Declaration |
| Toxic heavy metal free   | Yes                            |

|                            |                                                                                                                                                                                                                                |
|----------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Mercury free               | Yes                                                                                                                                                                                                                            |
| China RoHS Regulation      | <a href="#">China RoHS Declaration</a>                                                                                                                                                                                         |
| RoHS exemption information | <a href="#">Yes</a>                                                                                                                                                                                                            |
| Environmental Disclosure   | <a href="#">Product Environmental Profile</a>                                                                                                                                                                                  |
| Circularity Profile        | <a href="#">End Of Life Information</a>                                                                                                                                                                                        |
| WEEE                       | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins                                                                                                    |
| California proposition 65  | WARNING: This product can expose you to chemicals including: Styrene, which is known to the State of California to cause cancer. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a> |

## Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|