



## Main

Range	Canalis
Product name	KT
Product or component type	Connection adapter
Device short name	KTB
Product compatibility	KHF26 KHF28
Range compatibility	Canalis KT trunking Canalis KH trunking
[Ie] rated operational current	2500 A at 35 °C
Polarity	3L + N + PE
Earth conductor	Reinforced
Short-circuit level	Standard version
Length	850 mm

## Complementary

Network frequency	50/60 Hz
[Ui] rated insulation voltage	1000 V
Neutral position	Right
Width	600 mm
Height	466 mm
Colour	White (RAL 9001)
Net weight	80 kg

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	60.0 cm
Package 1 Width	60.0 cm
Package 1 Length	100.0 cm
Package 1 Weight	100.0 kg

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant with Exemptions
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End Of Life Information</a>

WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
PVC free	Yes