

LA1KN11

Auxiliary contact block, TeSys K, 1NO+1NC,
front mounting, screw clamp terminals



Main

Range	TeSys
Product name	TeSys K
Product or component type	Auxiliary contact block
Device short name	LA1
Range compatibility	TeSys K LC1K[RETURN]TeSys K CA2K[RETURN]TeSys K CA3K[RETURN]TeSys K CA4K
Mounting location	Front
Pole contact composition	1 NO + 1 NC
Contacts operation	Instantaneous
[Ue] rated operational voltage	690 V AC 25...400 Hz
[Ui] rated insulation voltage	690 V conforming to IEC 60947-5-1 600 V conforming to UL 60947-5-1 600 V conforming to CSA C22.2 No 60947-5-1
[Ith] conventional free air thermal current	10 A (at 50 °C)
Standards	EN/IEC 60947-5-1 UL 60947-5-1 CSA C22.2 No 60947-5-1 GB/T 14048.5 JIS C8201-5-1
Product certifications	CB Scheme[RETURN]CCC[RETURN]UL[RETURN]CSA[RETURN]CE

Complementary

Irms rated making capacity	110 A at <= 690 V AC conforming to IEC 60947
Permissible short-time rating	80 A 1 s 60 A 500 ms 110 A 100 ms
Associated fuse rating	10 A gG at <= 690 V conforming to IEC 60947
Minimum switching current	5 mA
Minimum switching voltage	17 V
Non overlap distance	0.5 mm
Insulation resistance	> 10 MOhm
Connections - terminals	Screw clamp terminals 1 cable(s) 0.34...1.5 mm ² flexible with cable end Screw clamp terminals 1 cable(s) 0.75...4 mm ² flexible without cable end Screw clamp terminals 1 cable(s) 1.5...4 mm ² rigid Screw clamp terminals 2 cable(s) 0.34...1.5 mm ² flexible with cable end Screw clamp terminals 2 cable(s) 0.75...4 mm ² flexible without cable end Screw clamp terminals 2 cable(s) 1.5...4 mm ² rigid
Tightening torque	1.3 N.M - with screwdriver Philips No 2 1.3 N.m - with screwdriver pozidriv No 2
Height	30 mm
Width	38 mm
Depth	35 mm
Net weight	0.045 kg

Environment

Environmental characteristic	Normal environment
IP degree of protection	IP20 conforming to IEC 60529
Protective treatment	TC conforming to IEC 60068
Ambient air temperature for storage	-50...80 °C
Ambient air temperature for operation	-25...50 °C
Operating altitude	2000 m

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.972 cm
Package 1 Width	3.403 cm
Package 1 Length	3.895 cm
Package 1 Weight	31.48 g
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	4.072 cm
Package 2 Width	11.143 cm
Package 2 Length	16.648 cm
Package 2 Weight	320.0 g
Unit Type of Package 3	S02
Number of Units in Package 3	100
Package 3 Height	15.0 cm
Package 3 Width	30.0 cm
Package 3 Length	40.0 cm
Package 3 Weight	3.75 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	No need of specific recycling operations
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	18 meseci
----------	-----------