



Main

Range	Acti9
Product name	Acti9 SBI
Product or component type	Fuse-disconnector
Device short name	SBI
Poles description	1N

Complementary

[In] rated current	10 A 16 A 20 A 25 A 32 A 12 A 40 A 50 A
Fuse curve	AM GG
Fuse size	14 x 51 mm
[Ue] rated operational voltage	690 V AC
Mounting support	35 mm symmetrical DIN rail
Locking options description	Non padlockable
9 mm pitches	3
Height	107 mm
Width	26.5 mm
Depth	70 mm
Connections - terminals	Screw clamp terminals1 cable(s) 2.5...25 mm² rigid Screw clamp terminals1 cable(s) 2.5...25 mm² flexible
Tightening torque	3.5 N.m

Environment

Standards	IEC EN 60947-3
Pollution degree	3
Ambient air temperature for operation	-20...60 °C
Ambient air temperature for storage	-40...80 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.8 cm
Package 1 Width	11.1 cm
Package 1 Length	7.6 cm
Package 1 Weight	124 g
Unit Type of Package 2	BB1
Number of Units in Package 2	6

Package 2 Height	7.9 cm
Package 2 Width	11.3 cm
Package 2 Length	16.4 cm
Package 2 Weight	820 g
Unit Type of Package 3	S03
Number of Units in Package 3	24
Package 3 Height	30 cm
Package 3 Width	30 cm
Package 3 Length	40 cm
Package 3 Weight	3.727 kg

Offer Sustainability

EU RoHS Directive	Compliant  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	18 months
----------	-----------