



Main

Range of product	Unica
Aesthetic name	Unica (standard aesthetic)
Product or component type	Push-button
Device presentation	Mechanism
Technology type	Electromechanical
Switch function	1-pole 1-way
Number of rocker	1
Device application	Bell switch
Colour tint	White

Complementary

Rated current	10 A
[Ue] rated operational voltage	250 V
Network type	AC
Network frequency	50/60 Hz
Electrical durability	40000 cycles, cos phi = 0.6
Insulation resistance	> 5 MOhm at 500 V
Dielectric strength	2000 V
Minimum load breaking capacity	200 operations 1.25 In and 1.1 Un, cos phi = 0.3
Condition of use	Impulse relay control
Opening distance	> 3 mm
Actuator	Push-button
Number of modules	1 module
Connections - terminals	Screwless terminals
Cable cross section	0...2.5 Mm² rigid cable 0...2.5 mm² flexible cable
Material	ASA + PC: mechanism cover ABS (acrylonitrile butadiene-styrene): mechanism cover
Marking	Bell symbol
Fixing mode	Clip-in
Width	22.5 mm
Height	45 mm
Depth	34 mm
Embedding depth	22 mm
Net weight	0.0173 kg
Ambient air temperature for operation	25...35 °C
Ambient air temperature for storage	0...50 °C
Standards	LV directive EMC directive EN 60669-1






Environment

IP degree of protection	IP20
IK degree of protection	IK01
Environmental characteristic	Window-cleaning fluid Alcohol Acetone Liquid soap Petrol UV resistant Oil Bleach

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	6.7 cm
Package 1 Width	4.4 cm
Package 1 Length	6.8 cm
Package 1 Weight	28.0 g
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	4.4 cm
Package 2 Width	13.6 cm
Package 2 Length	33.5 cm
Package 2 Weight	280.0 g
Unit Type of Package 3	S02
Number of Units in Package 3	40
Package 3 Height	15.0 cm
Package 3 Width	30.0 cm
Package 3 Length	40.0 cm
Package 3 Weight	1.12 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	No need of specific recycling operations
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	18 months
----------	-----------