



Main

Range of product	Unica
Aesthetic name	Unica (standard aesthetic)
Product or component type	Push-button
Device presentation	Mechanism
Technology type	Electromechanical
Switch function	1-pole 1-way
Number of rocker	1
Device application	Light control
Colour tint	Ivory

Complementary

Rated current	10 A
[Ue] rated operational voltage	250 V
Network type	AC
Network frequency	50/60 Hz
Electrical durability	40000 cycles, cos phi = 0.6
Insulation resistance	> 5 MOhm at 500 V
Dielectric strength	2000 V
Minimum load breaking capacity	200 operations 1.25 In and 1.1 Un, cos phi = 0.3
Condition of use	Impulse relay control
Opening distance	> 3 mm
Actuator	Push-button
Number of modules	1 module
Connections - terminals	Screwless terminals
Cable cross section	0...2.5 Mm² rigid cable 0...2.5 mm² flexible cable
Material	ASA + PC: mechanism cover
Marking	Light symbol
Fixing mode	Clip-in
Width	22.5 mm
Height	45 mm
Depth	34 mm
Embedding depth	22 mm
Net weight	0.0173 kg
Ambient air temperature for operation	25...35 °C
Ambient air temperature for storage	0...50 °C
Standards	EN 60669-1 EMC directive LV directive

The information provided in this documentation contains general descriptions and/or technical characteristics of the products of the company Schneider Electric. This information is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.






Environment

IP degree of protection	IP20
IK degree of protection	IK01
Environmental characteristic	Bleach Oil UV resistant Window-cleaning fluid Acetone Petrol Liquid soap Alcohol

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.4 cm
Package 1 Width	6.7 cm
Package 1 Length	6.8 cm
Package 1 Weight	28.0 g
Unit Type of Package 2	CAR
Number of Units in Package 2	10
Package 2 Height	4.4 cm
Package 2 Width	13.6 cm
Package 2 Length	33.5 cm
Package 2 Weight	280.0 g

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	No need of specific recycling operations
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	18 months
----------	-----------