



## Main

Range	Unica
Product or component type	Shutter control
Aesthetic name	Unica (standard aesthetic)
Device presentation	Mechanism
Rated current	10 A
[Ue] rated operational voltage	250 V
Network type	AC
Network frequency	50/60 Hz
Fixing mode	Clip-in
Colour tint	Ivory

## Complementary

Device mounting	Flush
Number of modules	1 module
Technology type	Electromechanical
Actuator	Push-button
Number of rocker	2
Switch function	1-pole 2-way
Switch application	Roller blind
Contacts type and composition	1 C/O
Mechanical interlocking	Interlock between up/down
[Iu] rated interrupted current	2.5 A for motor
Opening distance	> 3 mm
Marking	UP Down
Connections - terminals	Screw terminals
Cable cross section	2.5 Mm <sup>2</sup> flexible cable 2.5 mm <sup>2</sup> rigid cable
Minimum load breaking capacity	200 operations 1.25 I <sub>n</sub> and 1.1 I <sub>n</sub> , cos phi = 0.3
Electrical durability	10000 cycles, cos phi = 0.6
Insulation resistance	> 5 MOhm at 500 V
Dielectric strength	2000 V
Material	ASA + PC: mechanism cover
Standards	LV directive EMC directive EN 60669-1
Ambient air temperature for operation	25...35 °C
Ambient air temperature for storage	0...50 °C
Embedding depth	21 mm
Depth	33 mm
Width	22.4 mm
Height	45 mm

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

## Environment

IK degree of protection	IK01
IP degree of protection	IP20
Environmental characteristic	Petrol Bleach Oil Window-cleaning fluid Liquid soap Alcohol Acetone UV resistant

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.000 cm
Package 1 Width	6.500 cm
Package 1 Length	6.500 cm
Package 1 Weight	29.000 g
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	6.500 cm
Package 2 Width	12.500 cm
Package 2 Length	18.500 cm
Package 2 Weight	345.000 g
Unit Type of Package 3	S02
Number of Units in Package 3	80
Package 3 Height	15.000 cm
Package 3 Width	30.000 cm
Package 3 Length	40.000 cm
Package 3 Weight	2.985 kg

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 <a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>
RoHS exemption information	 <a href="#">Yes</a>
Environmental Disclosure	 <a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

## Contractual warranty

Warranty	18 months
----------	-----------