



### Main

Range	Unica
Product or component type	Telephone socket
Device presentation	Mechanism
Colour tint	White
Telephone socket type	RJ11 (4 contacts) - category 3 at 16 Mbit/s

### Complementary

Socket number	1
Number of modules	1 module
Connections - terminals	Screw terminals twisted pair
Fixing mode	Clip-in
Material	ASA + PC: mechanism cover
Depth	23 mm
Width	22.5 mm
Height	45 mm
Embedding depth	12 mm
Net weight	0.013 kg
Ambient air temperature for operation	15...30 °C
Ambient air temperature for storage	0...35 °C

### Environment

IP degree of protection	IP20
IK degree of protection	IK01
Environmental characteristic	Acetone Window-cleaning fluid Liquid soap Bleach Oil Alcohol Petrol

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	16.0 g
Package 1 Height	4.5 cm
Package 1 width	6.6 cm
Package 1 Length	6.6 cm
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Weight	225.0 g
Package 2 Height	4.6 cm
Package 2 width	13.5 cm

Package 2 Length	33.2 cm
Unit Type of Package 3	S03
Number of Units in Package 3	120
Package 3 Weight	3.146 kg
Package 3 Height	30.0 cm
Package 3 width	30.0 cm
Package 3 Length	40.0 cm

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

### Contractual warranty

Warranty	18 months
----------	-----------