



### Main

|                           |   |
|---------------------------|---|
| Range                     | Unica                                       |
| Product or component type | Telephone socket                            |
| Device presentation       | Mechanism                                   |
| Colour tint               | White                                       |
| Telephone socket type     | RJ11 (4 contacts) - category 3 at 16 Mbit/s |

### Complementary

|                                       |                              |
|---------------------------------------|------------------------------|
| Socket number                         | 1                            |
| Number of modules                     | 2 modules                    |
| Connections - terminals               | Screw terminals twisted pair |
| Fixing mode                           | Clip-in                      |
| Material                              | ASA + PC: mechanism cover    |
| Depth                                 | 23 mm                        |
| Width                                 | 45 mm                        |
| Height                                | 45 mm                        |
| Embedding depth                       | 12 mm                        |
| Net weight                            | 0.016 kg                     |
| Ambient air temperature for operation | 15...30 °C                   |
| Ambient air temperature for storage   | 0...35 °C                    |

### Environment

|                              |   |
|------------------------------|---|
| IP degree of protection      | IP20  |
| IK degree of protection      | IK01  |
| Environmental characteristic | Alcohol<br>Petrol<br>Oil<br>Bleach<br>Liquid soap<br>Window-cleaning fluid<br>Acetone |

### Packing Units

|                              |         |
|------------------------------|---------|
| Unit Type of Package 1       | PCE     |
| Number of Units in Package 1 | 1       |
| Package 1 Height             | 4.5 cm  |
| Package 1 Width              | 6.6 cm  |
| Package 1 Length             | 6.6 cm  |
| Package 1 Weight             | 19.0 g  |
| Unit Type of Package 2       | BB1     |
| Number of Units in Package 2 | 10      |
| Package 2 Height             | 4.6 cm  |
| Package 2 Width              | 13.5 cm |
| Package 2 Length             | 33.2 cm |

|                              |          |
|------------------------------|----------|
| Package 2 Weight             | 254.0 g  |
| Unit Type of Package 3       | S03      |
| Number of Units in Package 3 | 120      |
| Package 3 Height             | 30.0 cm  |
| Package 3 Width              | 30.0 cm  |
| Package 3 Length             | 40.0 cm  |
| Package 3 Weight             | 3.536 kg |

### Offer Sustainability

|                            |   |
|----------------------------|---|
| Sustainable offer status   | Green Premium product   |
| REACH Regulation           |  <a href="#">REACH Declaration</a>             |
| REACH free of SVHC         | Yes   |
| EU RoHS Directive          | Compliant  <a href="#">EU RoHS Declaration</a> |
| Toxic heavy metal free     | Yes   |
| Mercury free               | Yes   |
| China RoHS Regulation      |  <a href="#">China RoHS Declaration</a>        |
| RoHS exemption information |  <a href="#">Yes</a>                           |
| Circularity Profile        | No need of specific recycling operations  |
| WEEE                       | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins     |

### Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|