



### Main

Range	Unica
Device application	Mounting
Product or component type	Cover frame
Aesthetic name	Unica Allegro
Number of modules	3 modules
Fixing mode	Clip-in
Cover frame colour tint	Ivory

### Complementary

Material	ASA + PC: cover frame
Standards	EN 60669-1
Height	80 mm
Width	116 mm
Depth	14 mm
Net weight	0.019 kg
Market segment	Residential Small commercial

### Environment

IK degree of protection	IK01
IP degree of protection	IP20
Environmental characteristic	Window-cleaning fluid Acetone Petrol Oil Alcohol UV resistant Bleach Liquid soap

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.2 cm
Package 1 Width	11.9 cm
Package 1 Length	8.6 cm
Package 1 Weight	18 g
Unit Type of Package 2	BB1
Number of Units in Package 2	20
Package 2 Height	12.5 cm
Package 2 Width	18 cm
Package 2 Length	26 cm
Package 2 Weight	488 g
Unit Type of Package 3	S03
Number of Units in Package 3	80

Package 3 Height	30 cm
Package 3 Width	30 cm
Package 3 Length	40 cm
Package 3 Weight	2.121 kg

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations

### Contractual warranty

Warranty	18 months
----------	-----------