



Main

| | |
|-----------------------------|-------------------|
| Range | Resi9 |
| Product name | Resi9 MP |
| Product or component type | Enclosure |
| Enclosure type | Modular enclosure |
| Nb of 18 mm modules per row | 18 |
| Nb of horizontal rows | 1 |
| Type of door | Translucid |
| Width | 376 mm outside: |
| Height | 228 mm outside: |
| Depth | 103 mm outside: |

Complementary

| | |
|-------------------------------|--|
| Enclosure mounting | Surface |
| 9 mm pitches | 36 |
| Total number of 18 mm modules | 18 |
| [In] rated current | 63 A |
| Type of rail | 35 mm asymmetrical rail |
| Mounting plate description | Without mounting plate |
| Cable entry | 1 trunking flange 1 bare flange |
| Terminal block function | Earth / neutral |
| Number of terminal blocks | 1 earth (screwed) with 16 outgoing 1 neutral (screwed) with 16 outgoing |
| Distribution block outgoing | 2 x 16 mm ² for earth 2 x 16 mm ² for neutral 6 x 6 mm ² for earth 6 x 6 mm ² for neutral 8 x 10 mm ² for earth 8 x 10 mm ² for neutral |
| Enclosure material | Back part: technoplastic Door: technoplastic Front face: technoplastic |
| Internal depth | 80 mm |
| Colour | Front face: white (RAL 9003) Door: translucid |
| Market segment | Residential Small commercial |

Environment

| | |
|---------------------------------------|---|
| Standards | IEC 61439-1 IEC 61439-3 IEC 60670-1 IEC 60670-24 |
| Quality labels | IMQ |
| Fire resistance | Door: 650 °C Back part: 650 °C Front face: 650 °C |
| IP degree of protection | IP40 |
| IK degree of protection | IK07 |
| Ambient air temperature for operation | -25...60 °C |

Packing Units

| | |
|------------------------------|----------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Height | 10 cm |
| Package 1 Width | 23 cm |
| Package 1 Length | 37.5 cm |
| Package 1 Weight | 1.098 kg |
| Unit Type of Package 2 | BB1 |
| Number of Units in Package 2 | 5 |
| Package 2 Height | 30 cm |
| Package 2 Width | 40 cm |
| Package 2 Length | 52 cm |
| Package 2 Weight | 5.6 kg |
| Unit Type of Package 3 | P12 |
| Number of Units in Package 3 | 80 |
| Package 3 Height | 120 cm |
| Package 3 Width | 80 cm |
| Package 3 Length | 120 cm |
| Package 3 Weight | 101.6 kg |

Offer Sustainability

| | |
|-----------------------------|--|
| Sustainable offer status | Green Premium product |
| REACH Regulation | REACH Declaration |
| EU RoHS Directive | Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration |
| Mercury free | Yes |
| RoHS exemption information | Yes |
| China RoHS Regulation | China RoHS Declaration |
| Environmental Disclosure | Product Environmental Profile |
| Halogen content performance | Halogen free product |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|