

MIP12212S

Enclosure, Resi9 MP, surface mounting, 2 rows of 12 modules, IP40, smoked door, 1 earth + 1 neutral terminal blocks



Main

Range	Resi9
Product name	Resi9 MP
Product or component type	Enclosure
Enclosure type	Modular enclosure
Nb of 18 mm modules per row	12
Nb of horizontal rows	2
Type of door	Smoked
Width	Outside: 268 mm
Height	Outside: 353 mm
Depth	102 mm outside:

Complementary

Enclosure mounting	Surface
9 mm pitches	24
Total number of 18 mm modules	24
[In] rated current	63 A
Type of rail	35 mm asymmetrical rail
Mounting plate description	Without mounting plate
Cable entry	1 trunking flange 1 bare flange
Terminal block function	Earth / neutral
Number of terminal blocks	1 earth (screwed) with 16 outgoers 1 neutral (screwed) with 16 outgoers
Distribution block outgoers	2 x 16 mm ² for earth 2 x 16 mm ² for neutral 6 x 6 mm ² for earth 6 x 6 mm ² for neutral 8 x 10 mm ² for earth 8 x 10 mm ² for neutral
Enclosure material	Back part: technoplastic Door: technoplastic Front face: technoplastic
Internal depth	80 mm
Colour	Front face: white (RAL 9003) Door: smoked (RAL 9003)
Market segment	Residential Small commercial

The information provided in this documentation contains general descriptions and/or technical characteristics of the products of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Environment

Standards	IEC 61439-1 IEC 61439-3 IEC 60670-1 IEC 60670-24
Quality labels	IMQ
Fire resistance	Door: 650 °C Back part: 650 °C Front face: 650 °C
IP degree of protection	IP40
IK degree of protection	IK07
Ambient air temperature for operation	-25...60 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	10.000 cm
Package 1 Width	27.000 cm
Package 1 Length	35.500 cm
Package 1 Weight	1.217 kg
Unit Type of Package 2	S04
Number of Units in Package 2	5
Package 2 Height	30.000 cm
Package 2 Width	40.000 cm
Package 2 Length	60.000 cm
Package 2 Weight	7.007 kg
Unit Type of Package 3	P12
Number of Units in Package 3	80
Package 3 Height	119.000 cm
Package 3 Width	80.000 cm
Package 3 Length	120.000 cm
Package 3 Weight	124.112 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	No need of specific recycling operations
Halogen content performance	Halogen free product

Contractual warranty

Warranty	18 months
----------	-----------