

MIP22112

Enclosure, Resi9 MP, flush mounting, 1 row of 12 modules, IP40, white door, 1 earth + 1 neutral terminal blocks



Main

Range	Resi9
Product name	Resi9 MP
Product or component type	Enclosure
Enclosure type	Modular enclosure
Nb of 18 mm modules per row	12
Nb of horizontal rows	1
Type of door	Plain
Width	Wall: 270 mm Outside: 294 mm
Height	Wall: 228 mm Outside: 252 mm
Depth	18 Mm outside: 80 Mm wall: 98 mm total:

Complementary

Enclosure mounting	Flush
9 mm pitches	24
Total number of 18 mm modules	12
[In] rated current	63 A
Type of rail	35 mm asymmetrical rail
Mounting plate description	Without mounting plate
Cable entry	Pre-cutted holes
Terminal block function	Earth / neutral
Number of terminal blocks	1 earth (screwed) with 8 outgoing 1 neutral (screwed) with 8 outgoing
Distribution block outgoing	1 x 16 mm ² for earth 1 x 16 mm ² for neutral 3 x 6 mm ² for earth 3 x 6 mm ² for neutral 4 x 10 mm ² for earth 4 x 10 mm ² for neutral
Enclosure material	Back part: technoplastic Door: technoplastic Front face: technoplastic
Internal depth	76 mm
Colour	Door: white (RAL 9003) Front face: white (RAL 9003)
Market segment	Residential Small commercial

The information provided in this documentation contains general descriptions and/or technical characteristics of the products of the company. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Environment

Standards	IEC 61439-1 IEC 61439-3 IEC 60670-1 IEC 60670-24
Quality labels	IMQ
Fire resistance	Door: 650 °C Back part: 650 °C Front face: 650 °C
IP degree of protection	IP40
IK degree of protection	IK07
Ambient air temperature for operation	-25...60 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	9.800 cm
Package 1 Width	29.400 cm
Package 1 Length	25.200 cm
Package 1 Weight	873.000 g
Unit Type of Package 2	BB1
Number of Units in Package 2	8
Package 2 Height	52.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	7.912 kg
Unit Type of Package 3	P12
Number of Units in Package 3	128
Package 3 Height	120.000 cm
Package 3 Width	80.000 cm
Package 3 Length	120.000 cm
Package 3 Weight	138.600 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	No need of specific recycling operations
Halogen content performance	Halogen free product

Contractual warranty

Warranty	18 months
----------	-----------