



### Main

Range	Thalassa
Accessory / separate part category	Mounting accessory
Application	Modular distribution application Multi-purpose
Product or component type	Chassis
Device short name	DLP
For enclosure nominal dimensions	- H: 1500 mm W: 750 mm
Mounting location	Front of enclosure
Range compatibility	Thalassa Thalassa PLA
Device composition	1 chassis structure 1 neutral/earth strip 2 x 16 mm <sup>2</sup> 5 x 6 mm <sup>2</sup> 9 front panels with 35 mm DIN rail
Additional information	IP2x not respected when chassis is mounted at 67 mm

### Complementary

Material	Front panel: self-extinguishing Chassis structure and rails: galvanised steel
Colour	Front panel: grey (RAL 7032)
Fixing mode	By fixing element - on front with supports location
Adjustment	In height from 40 to 85 mm for DIN rail
Number of horizontal rows	9
Total number of 18 mm modules	297
Type of front plate	Cut-out plate
Number of cut-out	9 cut-outs
Height	Nominal: 1500 mm Real: 1427 mm
Width	Nominal: 750 mm Real: 666 mm
Depth	135 mm real:

### Contractual warranty

Warranty	18 months
----------	-----------