



Main

Range	Spacial
Application	Outdoor heavy duty
Accessory / separate part categor	Enclosure accessory
Product or component type	Ventilated roof
Device application	Multi-purpose
Mounting location	On top of enclosure
Range compatibility	Spacial Spacial SFHD suitable enclosure
Quantity per set	Set of 1

Complementary

Material	Steel with anti-corrosive coating
Colour	Grey (RAL 7035)
Surface finish	Polyester powder
Fixing mode	By screws - screw type M12 - roof fixing point location
Corrosion resistance	90...100 % conforming to ISO 12944 C4H
Height	95 mm
Width	1200 mm
Depth	600 mm
IP degree of protection	IP55 conforming to IEC 60529

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	9.5 cm
Package 1 Width	65.0 cm
Package 1 Length	125.0 cm
Package 1 Weight	13.944 kg
Unit Type of Package 2	P12
Number of Units in Package 2	5
Package 2 Height	77.0 cm
Package 2 Width	80.0 cm
Package 2 Length	120.0 cm
Package 2 Weight	82.8 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes

Environmental Disclosure	 Product Environmental Profile
Circularity Profile	No need of specific recycling operations