



## Main

Range	Spacial
Extended range	Spacial SF
Application	Prisma application
Product or component type	Suitable enclosure
Enclosure nominal height	2000 mm
Enclosure nominal width	700 mm
Enclosure nominal depth	800 mm
Enclosure mounting	Floor-standing
Product specific application	Installing the Prisma Plus System P
Device composition	2 sliding rails 4 mounting plate bracket 1 structure 1 door 1 locking system with handle: door 1 rear panel 1 roof 2 adaptor upright 2 intermediate upright

## Complementary

Structure type	Formed from a single section Vertical uprights joined with top and bottom frames Perforated structure with a pitch of 25 mm Panels and doors built into the structure
Door opening side	Reversible (120 °)
Door type	Plain front
Mounting plate description	Without mounting plate
Type of gland plate	Without gland plate
Lock type	4 points lock, handle with 5 mm double bar insert front door
Number of doors	Front: 1 door(s)
Accessibility for operation	Rear Front Sides of enclosure
Removable parts	Door by screws hinge Rear panel by screws Roof by screws Mounting plate bracket by screws Sliding rail by screws Adaptor upright by screws Intermediate upright
Material	Frame: galvanised steel Uprights: galvanised steel Door: sheet steel Panels: sheet steel Hinge: zamak Handle: polyamide 6 with 30 % fibre glass
Surface finish	Epoxy-polyester powder
Colour	Enclosure: grey (RAL 7035) Handle: black (RAL 9005)

## Environment

Standards	IEC 62208
IP degree of protection	IP55 conforming to IEC 60529
IK degree of protection	IK10 conforming to IEC 62262

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	75 cm
Package 1 Width	90 cm
Package 1 Length	215 cm
Package 1 Weight	90 kg

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>

## Contractual warranty

Warranty	18 months
----------	-----------