



Main

Range	PratiKa
Product or component type	Wander plug
Device short name	PratiKa plug
Plug, socket category	Low voltage
Poles description	3P + N + E
Network type	AC
Outlet standard	Industrial

Complementary

Plug, socket, control station shape	Straight
[In] rated current	32 A
[Ue] rated operational voltage	380...415 V
Network frequency	50/60 Hz
Ground lug clockwise position	6 h
Plug, socket material	Housing: self-extinguishing engineering polymer
Contacts material	Sleeves: brass
Connections - terminals	Captive screws
Cable cross section	2.5...10 mm ²
Cable outer diameter	11.5...21 mm
Cable entry	Cable gland Fair lead
Thread type	Pg 21
Net weight	0.25 kg
Height	160 mm
Width	86 mm
Depth	86 mm
Colour	Grey (RAL 7035)
Voltage colour	Red

Environment

Standards	IEC 60309-2 IEC 60309-1
IP degree of protection	IP44 conforming to IEC 60529
IK degree of protection	IK08 conforming to EN 62262
Fire resistance	850 °C conforming to IEC 60695-2-11
Relative humidity	50 % at 40 °C 70 % at 30 °C 90 % at 20 °C
Operating altitude	2000 m
Ambient air temperature for operation	35 °C (86400 s) -25...40 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	263.8 g
Package 1 Height	6.8 cm
Package 1 width	8.5 cm
Package 1 Length	16.6 cm
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Weight	2.798 kg
Package 2 Height	17.8 cm
Package 2 width	26.5 cm
Package 2 Length	26.7 cm
Unit Type of Package 3	S03
Number of Units in Package 3	20
Package 3 Weight	6.101 kg
Package 3 Height	30 cm
Package 3 width	30 cm
Package 3 Length	40 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------