

Main

Range of product	Altivar
Product or component type	Encoder interface card
Range compatibility	Altivar 61 Plus Altivar 71 Plus
Discrete output type	Differential
Communication port protocol	RS422
[Us] rated supply voltage	5 V DC (voltage limits: 5...5.5 V)
Number of pulses per revolution	10000 5000

Complementary

Maximum supply current	0.2 A
Protection type	Overload protection Short-circuit protection
Maximum cable distance between devices	50 m
Maximum operating frequency	300 kHz
Input signal	A B Compliment of A Compliment of B
Input impedance	440 Ohm
Electrical connection	Terminal, connection capacity: 0.2 mm ² (AWG 24) <25 m cable length, encoder, 100 mA at 4.5 V Terminal, connection capacity: 0.5 mm ² (AWG 20) <25 m cable length, encoder, 200 mA at 4.5 V Terminal, connection capacity: 0.5 mm ² (AWG 20) <50 m cable length, encoder, 100 mA at 4.5 V Terminal, connection capacity: 0.75 mm ² (AWG 18) <50 m cable length, encoder, 200 mA at 4.5 V
Net weight	0.2 kg

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7.0 cm
Package 1 Width	17.0 cm
Package 1 Length	23.5 cm
Package 1 Weight	152.0 g

Contractual warranty

Warranty	18 months
----------	-----------