



Main

Range name	Cedar Plus
Product or component type	Socket-outlet
Outlet standard description	Side earth
Socket number	2
Delivery form	Complete product
Additional features	Shuttered
Cover plate color	White

Complementary

Installation	Surface
Power range	3680 W
Rated current	16 A at 250 V AC
Kind of terminals	Lift terminals
Terminal capacity	2 cable(s) 2.5 mm ²
Wire structure	Rigid Flexible
Wire stripping length	11 mm
Material of visible parts	PA6 FR850
Surface finish	Glossy
Height	79 mm
Width	132 mm
Depth	54 mm
Net weight	0.196 kg

Environment

Product certifications	VDE
IP degree of protection	IP44

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	5.500 cm
Package 1 Width	8.000 cm
Package 1 Length	14.000 cm
Package 1 Weight	202.800 g
Unit Type of Package 2	BB1
Number of Units in Package 2	5
Package 2 Height	9.500 cm
Package 2 Width	18.500 cm
Package 2 Length	27.000 cm
Package 2 Weight	1.104 kg
Unit Type of Package 3	S03

Number of Units in Package 3	30
Package 3 Height	30.000 cm
Package 3 Width	30.000 cm
Package 3 Length	40.000 cm
Package 3 Weight	7.045 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant with Exemptions
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	No need of specific recycling operations
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	18 months
----------	-----------