



### Main

Range	Exxact
Product or component type	Switch
Device application	Control
Technology type	Electromechanical
Quantity per set	Set of 5

### Complementary

Device presentation	Mechanism with fixing frame
Device mounting	Flush
Number of rocker	2
Switch function	1-pole 2-way
Switch pattern	[5]
Rated current	16 A
[Ue] rated operational voltage	250 V
Network type	AC
Colour	Anthracite
Connections - terminals	Screw terminals
Loop terminals	2
Shape of screw head	Pozidriv No 1 and combi
Clamping connection capacity	1 x 1.5...2 x 2.5 mm <sup>2</sup> for solid cable(s) 1 x 1.5...2 x 2.5 mm <sup>2</sup> for solid stranded cable(s)
Material	ABS (acrylonitrile butadiene-styrene)
Optional fixing mode	By claw kit: insert By screw: rocker
Embedding depth	15 mm
Height	71 mm
Width	71 mm
Projecting depth	18 mm

### Environment

Standards	EN 60669-1
Product certifications	NEMKO[RETURN]FIMKO[RETURN]SEMKO[RETURN]CE
IP degree of protection	IP20

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3 cm
Package 1 Width	7 cm
Package 1 Length	7 cm
Package 1 Weight	68 g

Contractual warranty

Warranty	18 months
----------	-----------