



Teknisk informasjon

Produktspekter	Harmony XB5
Produkt eller type komponent	Komplett kropp-/lysblokkmontering
Kortnavn utstyr	ZB5
Festebrakettmateriale	Plast
Salg per udelelig kvantitet	1
Tilkoblingsklemmer	Skrutilkobling, $\leq 2 \times 1,5 \text{ mm}^2$ med endehylse i samsvar med EN 60947-1 Skrutilkobling, $> 1 \times 0,22 \text{ mm}^2$ uten endehylse i samsvar med EN 60947-1
Lyskilde	Glødepære
Pæreholder	BA 9s
Lysblokkforsyning	Via integral transformert 1,2 VA 6 V

Komplementær

Bredde	30 mm
Høyde	42 mm
Dybde	55 mm
Klemmebeskrivelse ISO n°1	(X1-X2)PL
Vekt	0,099 kg
Tiltrekningsmoment	0,8...1,2 N.m i samsvar med EN 60947-1
Formen på skruhodet	Kryss kompatibel med Philips no 1 skrutrekker Kryss kompatibel med Pozidriv No 1 skrutrekker Hullet kompatibel med flat $\varnothing 4 \text{ mm}$ skrutrekker Hullet kompatibel med flat $\varnothing 5.5 \text{ mm}$ skrutrekker
[U] isolasjonsspenning	600 V (forurensningsgrad 3) i samsvar med EN 60947-1
[Uimp] Nominell impuls-spenning	6 kV i samsvar med EN 60947-1
Signaltype	Klar
[Us] merkespenning	440 - 480 V AC på 50/60 Hz
Montering av blokk	Frontmontering
Elektrisk sammensetningskode	P4 M9
Enhetens utseende	Basic sub-assemblies

Miljø

Overflatebeskyttelse	TH
Omgivelsestemperatur for lagring	-40...70 °C
Omgivelsestemperatur drift	-40...55 °C
Beskyttelsesgrad mot elektrisk støt	Klasse II i samsvar med IEC 60536
Standarder	EN/IEC 60947-5-1 EN/IEC 60947-5-4 EN/IEC 60947-1 CSA C22.2 No 14 JIS C8201-5-1 UL 508 JIS C8201-1

Produktsertifikater	LROS (Lloyds register of shipping) BV GL CSA DNV UL listet
Vibrasjonsmotstand	5 gn (f= 2...500 Hz) i samsvar med IEC 60068-2-6
Støtmotstand	30 gn (varighet = 18 ms) for halvsinusurve akselerasjon i samsvar med IEC 60068-2-27 50 gn (varighet = 11 ms) for halvsinusurve akselerasjon i samsvar med IEC 60068-2-27

Forpakkingsinformasjon

Enhetstype pakke 1	PCE
Antall enheter i pakke 1	1
Pakke 1 Høyde	3,6 cm
Pakke 1 Bredder	5,5 cm
Pakke 1 Vekt	9,2 cm
Package 1 Weight	95,0 g
Enhetstype pakke 2	S03
Antall enheter i pakke 2	100
Pakke 2 Høyde	30 cm
Pakke 2 Bredder	30 cm
Pakke 2 Lengde	40 cm
Pakke 2 Vekt	9,938 kg


Bærekraftig

Produktets miljøstatus	Green Premium miljømerket produkt
REACH-regelverk	REACH-erklæring
REACH fri for SVHC	Ja
EU RoHS-direktiv	Proaktivt i samsvar (Produktet inngår ikke i EUs RoHS direktivet) EU RoHS-erklæring
Kvikksølvfri	Ja
Informasjon om RoHS-unntak	Ja
Kinas RoHS-forskrift	Kinas RoHS-Erklæring
Miljøinformasjon	Produktmiljøprofil
Produktets livssyklus	Informasjon Om Levetidsslutt
WEEE	Innen EU må produktet avhendes i henhold til bestemte regler for avfallshåndtering og aldri kastes som husholdningsavfall.

Garantiperiode

Garanti	18 months
---------	-----------

Dimensions



Panel Cut-out for Pushbuttons, Switches and Pilot Lights (Finished Holes, Ready for Installation)

Connection by Screw Clamp Terminals or Plug-in Connectors or on Printed Circuit Board



- (1) Diameter on finished panel or support
- (2) For selector switches and Emergency stop buttons, use of an anti-rotation plate type ZB5AZ902 is recommended.
- (3) $\varnothing 22.5$ mm recommended ($\varnothing 22.3_0^{+0.4}$) / $\varnothing 0.89$ in. recommended ($\varnothing 0.88$ in. $_0^{+0.016}$)

Connections	a in mm	a in in.	b in mm	b in in.
By screw clamp terminals or plug-in connector	40	1.57	30	1.18
By Faston connectors	45	1.77	32	1.26
On printed circuit board	30	1.18	30	1.18

Detail of Lug Recess



- (1) Diameter on finished panel or support
- (2) For selector switches and Emergency stop buttons, use of an anti-rotation plate type ZB5AZ902 is recommended.
- (3) $\varnothing 22.5$ mm recommended ($\varnothing 22.3_0^{+0.4}$) / $\varnothing 0.89$ in. recommended ($\varnothing 0.88$ in. $_0^{+0.016}$)