

Product data sheet

Characteristics

G45CX

Exclusive - cooker control unit - 1 gang - white



Main

Range of product	Exclusive
Product or component type	Cooker control unit
Device presentation	Complete product
Outlet standard	British
Colour tint	White moulded matt
Quantity per set	Set of 10

Complementary

Rated current	45 A at 230 V AC 50 Hz
Number of gangs	1 gang
Pilot light	Without neon indicator
Fixing mode	By screws M3.5 x 30 mm
Connections - terminals	Screw terminals
Material	Urea (carbamide)
Type of installation	Indoor
Depth	36 mm
Width	86 mm
Height	86 mm
Net weight	0.16 kg

Environment




Standards	BS EN 60669-1 BS 4177 BS 5733
IP degree of protection	IP20

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	8.5 cm
Package 1 Width	3.5 cm
Package 1 Length	8.5 cm
Package 1 Weight	160 g
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	9.3 cm
Package 2 Width	18 cm
Package 2 Length	19.5 cm
Package 2 Weight	1.71 kg
Unit Type of Package 3	CAR

Number of Units in Package 3	100
Package 3 Height	20 cm
Package 3 Width	41 cm
Package 3 Length	49 cm
Package 3 Weight	17.67 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant with Exemptions
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
Circularity Profile	 End Of Life Information

Contractual warranty

Warranty	18 months
----------	-----------