

7211840000

Kétjáratú menetes szabályzó szelep

V212T/40/25



Fő jellemzők

Valve product range	Venta
Termék vagy alkatrész típusa	Valve
Valve type	Globe
Valve product series	V212T
Valve model	V212T/40/25
Medium compatibility	Glycol 25 % Glycol 30 % Glycol 50 % Water
Valve configuration	2-Way
Valve connection type	Rp Internal
Valve connection size	Rp 1-1/2
Body size	40 mm (1-1/2 in)
Pipe size	40 mm
Flow characteristic	Equal percentage
Flow coefficient	28.91 cv 25 kvs
Pressure class	PN16
Operating fluid temperature	-20... 120 °C
Pressure fluid max delta P normal life	399,90 kPa
Control valve rangeability	Greater than 50:1
Stroke length	20 mm
Seat leakage	Port A: Class IV-S1 (0.005 %)
Stem flow action	Stem up closed
Stem movement	Linear
Trim material	Brass
Test anyaga	Nodular cast iron EN-JS 1030
Seat material	Port A: nodular cast iron EN-JS 1030
Stem material	Stainless steel AISI 303
Plug material	CW602N brass
Stem seal material	EPDM (ethylene propylene diene monomer)
Seating seal material	Port A:EPDM (ethylene propylene diene monomer)
Packing material	EPDM (ethylene propylene diene monomer)
Targeted region	Europe Asia Pacific. Australia.

Csomagolási egység

1. csomag-csomagolási egység típusa	PCE
Egységek száma 1. csomagban	1
1. csomag magassága	9,5 cm
1. csomag szélessége	15,0 cm
1. csomag hossza	23,5 cm
1. csomag súlya	2,807 kg

Kínálat fenntarthatósága

EU RoHS irányelv	Nem alkalmazható, nem tartozik az EU RoHS jogi hatálya alá
Kínai RoHS rendelet	 Kínai RoHS Nyilatkozat
Környezetvédelmi közzététel	 A Termék Környezeti Profilja
Körköröségi profil	Nincs szükség specifikus újrahasznosítási műveletekre