

7214114000

Kétjáratú menetes szabályzó szelep

V241/15/0.63



Fő jellemzők

Valve product range	Venta
Termék vagy alkatrész típusa	Valve
Valve type	Globe
Valve product series	V241
Valve model	V241/15/0.63
Medium compatibility	Glycol 25 % Glycol 30 % Glycol 50 % Water
Valve configuration	2-Way
Valve connection type	G External
Valve connection size	G 1B
Pipe size	15 mm
Body size	15 mm (1/2 in)
Flow characteristic	Equal percentage
Flow coefficient	0.73 cv 0.63 kvs
Pressure class	PN16
Operating fluid temperature	-20...150 °C
Pressure fluid max delta P normal life	599,84 kPa
Control valve rangeability	Greater than 50:1
Stroke length	20 mm
Seat leakage	Port A: Less than 0.02 % of kvs
Stem flow action	Stem up closed
Stem movement	Linear
Trim material	Stainless steel
Test anyaga	Bronze Rg5
Seat material	Port A: stainless steel AISI 303
Stem material	Stainless steel AISI 303
Plug material	Stainless steel AISI 303
Stem seal material	EPDM (ethylene propylene diene monomer)
Seating seal material	Port A: metal to metal
Packing material	EPDM (ethylene propylene diene monomer)
Targeted region	Europe Asia Pacific. Australia.

Csomagolási egység

1. csomag-csomagolási egység típusa	PCE
Egységek száma 1. csomagban	1
1. csomag magassága	5,0 cm
1. csomag szélessége	10,5 cm
1. csomag hossza	16,5 cm
1. csomag súlya	971,0 g

Kínai fenntarthatósága

EU RoHS irányelv	Nem alkalmazható, nem tartozik az EU RoHS jogi hatálya alá
Kínai RoHS rendelet	 Kínai RoHS Nyilatkozat
Környezetvédelmi közzététel	 A Termék Környezeti Profilja
Körköröségi profil	Nincs szükség specifikus újrahasznosítási műveletekre