



Main

Range	Unica
Product or component type	Socket-outlet
Aesthetic name	Unica (standard aesthetic)
Device presentation	Mechanism
Device mounting	Flush
Socket number	1
Outlet poles configuration	2P
Outlet standard deviation	European
Rated current	10 A

Complementary

Device application	Power supply
Cover type	With shutter
[Ue] rated operational voltage	250 V
Network type	AC
Network frequency	50/60 Hz
Number of modules	1 module
Fixing mode	Clip-in
Colour tint	White
Connections - terminals	Screw terminals
Cable cross section	0...4 mm ² - cable stiffness: flexible 0...4 mm ² - cable stiffness: rigid
Minimum load breaking capacity	100 operations 1.25 In and 1.1 Un, cos phi = 0.6
Electrical durability	10000 cycles, cos phi = 0.8
Insulation resistance	> 5 MOhm at 500 V
Dielectric strength	2000 V
Material	ASA + PC: mechanism cover
Quantity per set	Set of 1 blister
Product certifications	FR.ME63.B02375 AC
Embedding depth	27 mm
Depth	37 mm
Width	22.5 mm
Height	45 mm
Net weight	0.018 kg






Environment

Ambient air temperature for operation	15...30 °C
Ambient air temperature for storage	0...35 °C
IK degree of protection	IK01
IP degree of protection	IP20
Environmental characteristic	Bleach Petrol Alcohol Acetone Liquid soap Window-cleaning fluid Oil UV resistant

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.000 cm
Package 1 Width	6.500 cm
Package 1 Length	6.500 cm
Package 1 Weight	20.800 g
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	4.500 cm
Package 2 Width	13.500 cm
Package 2 Length	33.500 cm
Package 2 Weight	275.000 g
Unit Type of Package 3	S02
Number of Units in Package 3	40
Package 3 Height	15.000 cm
Package 3 Width	30.000 cm
Package 3 Length	40.000 cm
Package 3 Weight	1.334 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	No need of specific recycling operations
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	18 months
----------	-----------