



Main

Aesthetic name	Unica (standard aesthetic)
Product or component type	Loudspeaker socket
Device presentation	Mechanism
Colour tint	White

Complementary

Socket number	1
Number of modules	1 module
Connections - terminals	2 pressure fixing
Fixing mode	Clip-in
Material	ASA + PC: mechanism cover
Depth	37 mm
Width	22.5 mm
Height	45 mm
Net weight	0.014 kg

Environment

IP degree of protection	IP20
IK degree of protection	IK01
Ambient air temperature for operation	15...30 °C
Ambient air temperature for storage	0...35 °C
Environmental characteristic	Oil UV resistant Bleach Liquid soap Acetone Window-cleaning fluid Alcohol Petrol

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.000 cm
Package 1 Width	6.500 cm
Package 1 Length	6.500 cm
Package 1 Weight	18.400 g
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	4.500 cm
Package 2 Width	13.500 cm
Package 2 Length	33.000 cm

Package 2 Weight	243.000 g
Unit Type of Package 3	S02
Number of Units in Package 3	40
Package 3 Height	15.000 cm
Package 3 Width	30.000 cm
Package 3 Length	40.000 cm
Package 3 Weight	1.208 kg

Offer Sustainability

REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	18 months
----------	-----------