



Main

Aesthetic name	Unica Top - Unica Class
Product or component type	Dimmer
Device presentation	Mechanism
Fixing mode	Clip-in
[Ue] rated operational voltage	230 V AC 50 Hz
Number of modules	2 modules
Colour tint	Graphite

Complementary

Dimmer control	Rotary push type
Maximum permanent current	1.74 A
Total number of wires	2
Load type	230 V AC halogen lamp - 40...400 W 230 V AC incandescent lamp - 40...400 W Low voltage halogen lamp with ferromagnetic transformer - 40...400 VA
Protection type	Fuse protection
Fuse type	4 Ah 5 x 20 mm 230 V 50 Hz
Marking	L+N
Connections - terminals	Screw terminals
Clamping connection capacity	<= 2 x 2.5 mm ²
Connected auxiliaries	2-way switch
Material	ASA + PC: mechanism cover
Standards	EN 60669-2-1
Product certifications	CE
Ambient air temperature for operation	5...30 °C
Ambient air temperature for storage	-20...60 °C
Embedding depth	34 mm
Depth	54 mm
Width	45 mm
Height	45 mm
Net weight	0.071 kg


Environment

IK degree of protection	IK01
IP degree of protection	IP20
Environmental characteristic	Window-cleaning fluid Acetone Petrol Oil Bleach Alcohol UV resistant Liquid soap

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	6.5 cm
Package 1 Width	9.8 cm
Package 1 Length	10.8 cm
Package 1 Weight	124.0 g
Unit Type of Package 2	S02
Number of Units in Package 2	15
Package 2 Height	15.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	2.208 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	 End Of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	18 months
----------	-----------