



### Main

|                           |               |
|---------------------------|---------------|
| Range                     | Unica         |
| Device application        | Mounting      |
| Product or component type | Cover frame   |
| Aesthetic name            | Unica Allegro |
| Number of modules         | 6 modules     |
| Fixing mode               | Clip-in       |
| Cover frame colour tint   | White         |

### Complementary

|                |                                 |
|----------------|---------------------------------|
| Material       | ASA + PC: cover frame           |
| Standards      | EN 60669-1                      |
| Height         | 80 mm                           |
| Width          | 193 mm                          |
| Depth          | 14 mm                           |
| Net weight     | 0.025 kg                        |
| Market segment | Residential<br>Small commercial |

### Environment

|                              |                                                                                                       |
|------------------------------|-------------------------------------------------------------------------------------------------------|
| IK degree of protection      | IK01                                                                                                  |
| IP degree of protection      | IP20                                                                                                  |
| Environmental characteristic | Acetone<br>Window-cleaning fluid<br>UV resistant<br>Bleach<br>Oil<br>Petrol<br>Alcohol<br>Liquid soap |

### Packing Units

|                              |           |
|------------------------------|-----------|
| Unit Type of Package 1       | PCE       |
| Number of Units in Package 1 | 1         |
| Package 1 Height             | 1.500 cm  |
| Package 1 Width              | 8.000 cm  |
| Package 1 Length             | 19.500 cm |
| Package 1 Weight             | 28.000 g  |
| Unit Type of Package 2       | BB1       |
| Number of Units in Package 2 | 5         |
| Package 2 Height             | 7.500 cm  |
| Package 2 Width              | 9.500 cm  |
| Package 2 Length             | 25.000 cm |
| Package 2 Weight             | 195.000 g |
| Unit Type of Package 3       | S03       |
| Number of Units in Package 3 | 60        |

|                  |           |
|------------------|-----------|
| Package 3 Height | 30.000 cm |
| Package 3 Width  | 30.000 cm |
| Package 3 Length | 40.000 cm |
| Package 3 Weight | 2.721 kg  |

### Offer Sustainability

|                            |                                                            |
|----------------------------|------------------------------------------------------------|
| Sustainable offer status   | Green Premium product                                      |
| REACH Regulation           | <a href="#">REACH Declaration</a>                          |
| EU RoHS Directive          | Pro-active compliance (Product out of EU RoHS legal scope) |
| Mercury free               | Yes                                                        |
| China RoHS Regulation      | <a href="#">China RoHS Declaration</a>                     |
| RoHS exemption information | <a href="#">Yes</a>                                        |
| Environmental Disclosure   | <a href="#">Product Environmental Profile</a>              |
| Circularity Profile        | No need of specific recycling operations                   |

### Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|