



Main

Range of product	9007
Series name	Miniature potted
Product or component type	Limit switch lever
Device short name	9007MS/ML
Associated complete product	9007ML04.. 9007MS04..
Movement of operating head	Rotary
Type of operator	Cast zinc spring return roller lever length: 50.80 mm -
Type of roller	1 nylon outside roller diameter: 19.05 mm - width: 6.35 mm
Type of approach	Lateral approach
Positive opening	Without

Complementary

Tracks	1.375 in
Switch actuation	By 30° cam
Net weight	0.05 kg

Environment

Ambient air temperature for operation	-40...105 °C
Ambient air temperature for storage	-40...105 °C
Environmental characteristic	Standard environment

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	18.796 cm
Package 1 Width	17.272 cm
Package 1 Length	29.21 cm
Package 1 Weight	45.359 g

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
For all Reach Rohs enquiries contact us at	sustainability@tesensors.com

Contractual warranty

Warranty	18 months
----------	-----------