



Main

Range of product	9007
Series name	Miniature potted
Product or component type	Limit switch lever
Device short name	9007MS/ML
Associated complete product	9007ML04.. 9007MS04..
Movement of operating head	Rotary
Type of operator	Cast zinc spring return roller lever length: 44.45 mm -
Type of roller	1 nylon outside roller diameter: 19.05 mm - width: 12.70 mm
Type of approach	Lateral approach
Positive opening	Without

Complementary

Tracks	1.375 in
Switch actuation	By 30° cam
Net weight	0.05 kg

Environment

Ambient air temperature for operation	-40...105 °C
Ambient air temperature for storage	-40...105 °C
Environmental characteristic	Standard environment

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	18.796 cm
Package 1 Width	17.272 cm
Package 1 Length	29.21 cm
Package 1 Weight	45.359 g

Contractual warranty

Warranty	18 months
----------	-----------