



### Main

Range of product	9007
Series name	Heavy duty
Product or component type	Limit switch head
Device short name	9007C
Head type	Rotary head
Product compatibility	9007C
Associated lever	9007C
Associated body	9007C
Movement of operating head	Rotary
Type of operator	Spring return without operating lever zinc low differential
Type of approach	Lateral approach, 1 or 2 programmable direction
Positive opening	Without

### Complementary

Switch actuation	CW and CCW From left and right
Net weight	0.19 kg

### Environment

Ambient air temperature for operation	-29...85 °C
Ambient air temperature for storage	-29...85 °C
Environmental characteristic	Standard environment

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.6 cm
Package 1 Width	4.8 cm
Package 1 Length	7.6 cm
Package 1 Weight	190.5 g

### Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
For all Reach Rohs enquiries contact us at	<a href="mailto:sustainability@tesensors.com">sustainability@tesensors.com</a>

### Contractual warranty

Warranty	18 months
----------	-----------