



Main

Range of product	9007
Series name	Heavy duty
Product or component type	Snap limit switch operator
Device short name	9007AO/CO

Complementary

Operator profile	Plunger head
Fixing mode	By the head
Movement of operating head	Linear
Product compatibility	Snap basic limit switch
Type of operator	Spring return plunger metal
Switch actuation	On end
Type of approach	1 direction vertical approach
Width	21.08 mm
Height	63.50 mm
Depth	27.94 mm
Net weight	0.05 kg

Environment

NEMA degree of protection	NEMA 1 conforming to Nema type 250
IP degree of protection	IP20 conforming to IEC 60529
Ambient air temperature for operation	-29...85 °C
Ambient air temperature for storage	-29...85 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	6.452 cm
Package 1 Width	2.54 cm
Package 1 Length	16.387 cm
Package 1 Weight	45.359 g

Offer Sustainability

Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Diisodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
For all Reach Rohs enquiries contact us at	sustainability@tesensors.com

Contractual warranty

Warranty	18 months
----------	-----------