



Main

Range of product	9007
Series name	Heavy duty
Product or component type	Limit switch
Device short name	9007AW
Product specific application	Precision
Body type	Plug-in

Complementary

Mounting mode	Surface mounting
Operator profile	Plunger head
Material	Metal
Body material	Cast zinc
Operator material	Cast zinc
Fixing mode	By the body
Movement of operating head	Linear
Type of operator	Spring return roller plunger steel with micrometer adjustment
Switch actuation	By 30° cam
Type of approach	Traverse approach, 2 directions
Electrical connection	1...2 cables for screw-clamp terminals (AWG 22...AWG 12)
Cable entry	1 entry for 1/2" - 14 NPT conforming to ANSI B1.20.1
Number of poles	1
Contacts type and composition	NC-NO, switch function: SPDT-DB
Contact form	Form Z
Contact operation	Snap action
Number of steps	1
Contacts material	Silver contacts
Positive opening	Without
Terminals description ISO n°1	(3-4)NO (1-2)NC
Minimum force for tripping	3 lbf
Repeat accuracy	+/- 0.001 in
[Ie] rated operational current	5 A at 600 V AC, A600 conforming to NEMA rating designation 6 A at 480 V AC, A600 conforming to NEMA rating designation 10 A at 240 V AC, A600 conforming to NEMA rating designation 15 A at 120 V AC, A600 conforming to NEMA rating designation 0.02 A at 600 V DC 0.2 A at 250 V DC 0.5 A at 125 V DC
[Ithe] conventional enclosed thermal current	15 A
[Ui] rated insulation voltage	600 V (pollution degree 3) conforming to UL 508 for contact block 600 V conforming to CSA C22.2 No 14 for contact block
Width	64.26 mm
Height	93.47 mm
Depth	36.58 mm
Net weight	0.57 kg

Environment

NEMA degree of protection	NEMA 1 conforming to Nema type 250 NEMA 2 conforming to Nema type 250 NEMA 4 conforming to Nema type 250 NEMA 12 conforming to Nema type 250 NEMA 13 conforming to Nema type 250
IP degree of protection	IP65 conforming to IEC 60529
Ambient air temperature for operation	-18...85 °C
Ambient air temperature for storage	-18...85 °C
Protective treatment	Epoxy powder coat

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7.112 cm
Package 1 Width	13.208 cm
Package 1 Length	4.318 cm
Package 1 Weight	566.991 g
Unit Type of Package 2	CAR
Number of Units in Package 2	10
Package 2 Height	15.748 cm
Package 2 Width	18.796 cm
Package 2 Length	19.812 cm
Package 2 Weight	5.693 kg

Offer Sustainability

Environmental Disclosure	 Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
For all Reach Rohs enquiries contact us at	sustainability@tesensors.com

Contractual warranty

Warranty	18 months
----------	-----------